


Sampling: 44100 Hz
FFT size: 131072
Averaging: 1
Window: Hanning
Overlap: 0 %

Printed by: SpectraLAB - FFT Spectral Analysis System
Licensed to: boost
Sun Oct 30 02:28:16 2011


MOL315
Maxell UDI 50 jap



Sampling: 44100 Hz
FFT size: 131072
Averaging: 1
Window: Hanning
Overlap: 0 %

Printed by: SpectraLAB - FFT Spectral Analysis System
Licensed to: boost
Sun Oct 30 02:29:05 2011

MOL315
Ref.Level 250nWb



まっすぐな音。

POSITION: NORMAL

HIGH EFFICIENCY & HIGH RESONANCE-ABSORBING CASSETTE MECHANISM
SPINTECH 2-MAGNETIC PARTICLE FOR NORMAL POSITION

伝わる音楽の熱気。
中・低域の力感を再現。エネルギーサウンド。

- 音がシャキッと立ち上がる。高速磁化設計テープ採用。
- 新デザイン。ストリームライン(流線形)・ウインドウ・ハーフ。
- クリーニング・リーダーテープで、聴くたびにヘッドクリーニング。
- ヘッドホンステレオに最適。省電力カセットメカニズム。

品質には万全を期していますが、万一製造上の原因による品質不良がありました場合は、同数の新しいテープとお取りがえします。それ以外の責はご容赦ください。

タイムラインアップ	10	30	46	50		
54	60	64	70	74	90	120

日立マクセル株式会社
型番 UD1-50G



T4902580226749

50

UD1

MAXELL